


Garant
Parting-off / grooving insert, HU7310, Groove width w: 3mm

Order data

Order number	273697 3
GTIN	4045197580429
Item class	21L

Description

Parting-off / grooving insert 3 mm Tolerance groove width w: ± 0.03 mm
Feed f: 0.07 - 0.2 mm/rev.

Technical description

Groove width w	3 mm
Tolerance groove width w	± 0.03 mm
Feed f	0.07 - 0.2 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
Main application	N
Secondary application	Ti
Cutting conditions	continuous
Grade	HU7310
Corner radius R	0.2 mm
Number of changes/inserts	2

Indexable insert profile	neutral
Type of product	Indexable insert for grooving

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	350 m/min	N
Aluminium (short chipping)	suitable	350 m/min	N
Alu > 10% Si	suitable	280 m/min	N
Ti > 850 N/mm ²	suitable	50 m/min	S
continuous	suitable		
irregular	suitable only under restricted conditions		
wet maximum	suitable		