



CCMT indexable insert for medium machining 50 pieces, HBT130, Size: 09T304



Order data

Order number	GG2625 09T304
GTIN	4067263096269
Item class	GGN

Technical description

Coating	TiCN
Cutting depth a_p	0.3 - 3 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Quantity	50
Cutting depth $a_{p \max}$	3.25 mm
Corner radius	0.4 mm
Contents	260211 HBT130
Main application	M
ISO code indexable insert	CCMT 09T304
Cutting speed v_c main application	50 - 200 mm/min
Number of changes/inserts	2
Cutting depth $a_{p \min}$	0.25 mm

Feed f	0.05 - 0.35 mm/rev.
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2625 09T304