

**SCMT indexable insert for finishing 30 pieces, HB7010-2, Size: 09T304****Order data**

Order number	GG2827 09T304
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	SCMT 09T304
Cutting speed v_c main application	150 - 500 mm/min
Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.25 mm
Contents	260742 HB7010-2
Cutting depth $a_{p \max}$	3.25 mm
Feed f	0.07 - 0.25 mm/rev.
Tool material	Carbide
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Quantity	30
Type	HB7010-2

Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2827 09T304