

**Value pack DNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2426 110404
GTIN	4067263092810
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth $a_{p \min}$	0.25 mm
Main application	P
ISO code indexable insert	DNMG 150608
Contents	250752 HB7020-2
Cutting speed v_c main application	130 - 370 mm/min
Cutting depth a_p	0.3 - 4 mm
Number of changes/inserts	4
Corner radius	0.4 mm
Feed f	0.2 - 0.5 mm/rev.
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2426 110404
