


CCGT indexable insert for medium machining 50 pieces, HB7310, Size: 060202

Order data

Order number	GG3807 060202
GTIN	4067263097709
Item class	GGN

Technical description

Cutting depth a_p	0.1 - 4 mm
Cutting depth $a_{p \min}$	0.15 mm
Cutting depth $a_{p \max}$	2 mm
Feed f	0.05 - 0.5 mm/rev.
Main application	N
Tool material	Carbide
Contents	260140 HB7310
Cutting speed v_c main application	350 - 600 mm/min
Finishing/roughing assignment	Finishing
Quantity	50
Corner radius	0.2 mm
ISO code indexable insert	CCGT 060202
Number of changes/inserts	2
Tolerance	G

Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3807 060202