



DCMT indexable insert for finishing 30 pieces, HB7120-1, Size: 11T308



Order data

Order number	GG3513 11T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	90 - 290 mm/min
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth a_p	0.2 - 1.5 mm
ISO code indexable insert	DCMT 11T308
Main application	M
Tolerance	M
Tool material	Carbide
Contents	260361 HB7120-1
Number of changes/inserts	2
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Quantity	30

Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3513 11T308