

Garant**CCGT indexable insert for medium machining 50 pieces, HB7310, Size: 120408****Order data**

Order number	GG3807 120408
GTIN	4067263097846
Item class	GGN

Technical description

Contents	260160 HB7310
Main application	N
Cutting speed v_c main application	350 - 600 mm/min
Feed f	0.05 - 0.5 mm/rev.
Quantity	50
Corner radius	0.8 mm
Tool material	Carbide
Cutting depth a_p	0.1 - 4 mm
Number of changes/inserts	2
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	CCGT 120408
Cutting depth $a_{p \max}$	4.25 mm
Finishing/roughing assignment	Finishing
Tolerance	G

Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3807 120408