



## Short drill chuck Form A, SK 40, Clamping range: 2,5-16mm



### Order data

Order number	301490 2,5-16
GTIN	2050001690555
Item class	33W

### Description

#### Version:

For clockwise and anticlockwise rotation.

#### Supplied with:

Hexagon screwdriver with T-handle.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

Spare chuck key No. 627425	SW6
Overhang dimension A	95 mm
Clamping range	2.5 - 16 mm
External Ø D	57 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

---

## Accessories

Set of chuck jaws 3 pieces for chuck range 2,5-16 mm	309701 2,5-16
Pinion for chuck range 2,5-16 mm	309702 2,5-16