



TCMT indexable insert for medium machining 30 pieces, HBT130, Size: 110204



Order data

Order number	GG2684 110204
GTIN	4067263096931
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
ISO code indexable insert	TCMT 110204
Cutting depth $a_{p \min}$	0.25 mm
Cutting speed v_c main application	50 - 200 mm/min
Cutting depth $a_{p \max}$	2.75 mm
Number of changes/inserts	3
Coating	TiCN
Main application	M
Tool material	Carbide
Corner radius	0.4 mm
Feed f	0.05 - 0.35 mm/rev.
Cutting depth a_p	0.3 - 2.5 mm
Contents	261012 HBT130
Quantity	30

Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2684 110204