



## TCMT indexable insert for medium machining 50 pieces, HBT130, Size: 16T304



### Order data

|              |               |
|--------------|---------------|
| Order number | GG2687 16T304 |
| GTIN         | 4067263096962 |
| Item class   | GGN           |

### Technical description

|                                      |                     |
|--------------------------------------|---------------------|
| Feed f                               | 0.05 - 0.35 mm/rev. |
| Cutting depth $a_{p \min}$           | 0.25 mm             |
| Corner radius                        | 0.4 mm              |
| Quantity                             | 50                  |
| Cutting depth $a_{p \max}$           | 4 mm                |
| Number of changes/inserts            | 3                   |
| Tool material                        | Carbide             |
| Cutting speed $v_c$ main application | 50 - 200 mm/min     |
| Finishing/roughing assignment        | Finishing           |
| Main application                     | M                   |
| ISO code indexable insert            | TCMT 16T304         |
| Cutting depth $a_p$                  | 0.3 - 2.5 mm        |
| Contents                             | 261018 HBT130       |

|                    |                              |
|--------------------|------------------------------|
| Coating            | TiCN                         |
| Type               | HBT130                       |
| Cutting conditions | slightly interrupted         |
| Chip breaker       | MM                           |
| Type of product    | Indexable insert for turning |

**Suitable products**

No Shop URL available for: GG2687 16T304