

**DCMT indexable insert for finishing 30 pieces, HB7130-2, Size: 11T308****Order data**

Order number	GG3514 11T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	80 - 270 mm/min
Corner radius	0.8 mm
ISO code indexable insert	DCMT 11T308
Contents	260361 HB7130-2
Number of changes/inserts	2
Feed f	0.1 - 0.3 mm/rev.
Cutting depth $a_{p \text{ min}}$	0.55 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting depth $a_{p \text{ max}}$	2.75 mm
Cutting depth a_p	0.2 - 1.5 mm
Tolerance	M
Main application	M
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3514 11T308