

Garant**DCGT indexable insert for medium machining 30 pieces, HB7310, Size: 070202****Order data**

Order number	GG3815 070202
GTIN	4067263098058
Item class	GGN

Technical description

Contents	260449 HB7310
Number of changes/inserts	2
Main application	N
Cutting depth a_p	0.1 - 4 mm
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
Quantity	30
ISO code indexable insert	DCGT 070202
Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.2 mm
Cutting depth $a_{p \min}$	0.15 mm
Finishing/roughing assignment	Roughing
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	350 - 600 mm/min

Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3815 070202