



Short drill chuck Form A, SK 40, Clamping range: 1-13mm



Order data

Order number	301480 1-13
GTIN	4045197307620
Item class	37D

Description

Version:

For clockwise and anticlockwise rotation.
Burnished.

Supplied with:

Hexagon screwdriver with T-handle.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Overhang dimension A	87.5 mm
Spare chuck key No. 627425	SW6
Clamping range	1 - 13 mm
External Ø D	43 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 18,000 rpm
maximum tightening torque $M_{d\max}$	≤ 14 Nm
Type of product	Short drill chuck

Accessories

Pull studsealed suitable for steep tapers 40	308660 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed, form B suitable for steep tapers 40	308620 40
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Pull studForm B suitable for steep tapers 40	308640 40