



VCMT indexable insert for medium machining 50 pieces, HBT130, Size: 110304



Order data

Order number	GG2696 110304
GTIN	4067263097280
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2.5 mm
Feed f	0.05 - 0.35 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	2
Cutting speed v_c main application	50 - 200 mm/min
Cutting depth $a_{p \max}$	1.75 mm
Coating	TiCN
Tool material	Carbide
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
ISO code indexable insert	VCMT 110304
Main application	M

Quantity	50
Contents	261472 HBT130
Type	HBT130
Cutting conditions	slightly interrupted
Chip breaker	MM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2696 110304