


RCG. indexable insert for medium machining 30 pieces, HU730-1, Size: 1003

Order data

Order number	GG3819 1003
GTIN	4067263092278
Item class	GGN

Technical description

Coating	uncoated
Number of changes/inserts	2
Tolerance	G
Cutting speed v_c main application	350 - 600 mm/min
ISO code indexable insert	RCGX 1003
Feed f	0.1 - 0.3 mm/rev.
Cutting depth $a_{p \max}$	2 mm
Cutting depth $a_{p \min}$	0.5 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 2 mm
Tool material	Carbide
Main application	N
Quantity	30
Contents	260640 HU7310-1

Type	HU730-1
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3819 1003