

Garant**DCMT indexable insert for medium machining 30 pieces, HB7120-1, Size: 070202****Order data**

Order number	GG3519 070202
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	DCMT 070202
Cutting depth $a_{p \min}$	0.15 mm
Main application	M
Contents	260449 HB7120-1
Number of changes/inserts	2
Tool material	Carbide
Cutting depth a_p	0.5 - 2.5 mm
Tolerance	M
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	1.75 mm
Corner radius	0.2 mm
Cutting speed v_c main application	80 - 260 mm/min

Quantity	30
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3519 070202