



Short drill chuck Form A, SK 40, Clamping range: 0,3-8mm



Order data

Order number	301490 0,3-8
GTIN	2050001689504
Item class	33W

Description

Version:

For clockwise and anticlockwise rotation.

Supplied with:

Hexagon screwdriver with T-handle.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Clamping range	0.3 - 8 mm
Overhang dimension A	70 mm
Spare chuck key No. 627425	SW4
External Ø D	36 mm
Adapter	SK 40
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 30 µm
Type of product	Short drill chuck

Accessories

Pinion for chuck range 0,3-8 mm	309702 0,3-8
Set of chuck jaws 3 pieces for chuck range 0,3-8 mm	309701 0,3-8