

Garant**DCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 11T302****Order data**

Order number	GG3521 11T302
GTIN	4067263096375
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	2.75 mm
Tolerance	M
Contents	260458 HB7130-2
Cutting speed v_c main application	70 - 240 mm/min
ISO code indexable insert	DCMT 11T302
Corner radius	0.2 mm
Main application	M
Feed f	0.1 - 0.4 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \min}$	0.15 mm
Number of changes/inserts	2
Cutting depth a_p	0.5 - 2.5 mm
Coating	coated
Finishing/roughing assignment	Finishing

Data sheet

Quantity	30
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3521 11T302