

Garant**VBGT indexable insert for medium machining 30 pieces, HU7310, Size: 110301****Order data**

Order number	GG3827 110301
GTIN	4067263098379
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.05 mm
Feed f	0.05 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Coating	uncoated
Cutting speed v_c main application	350 - 600 mm/min
Main application	N
ISO code indexable insert	VBGT 110301
Cutting depth $a_{p \max}$	1.75 mm
Cutting depth a_p	0.1 - 4 mm
Number of changes/inserts	2
Tool material	Carbide
Corner radius	0.1 mm
Contents	261220 HU7310
Quantity	30

Tolerance	G
Type	HU7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3827 110301