

Garant**VBGT indexable insert for medium machining 30 pieces, HU7310, Size: 110304****Order data**

Order number	GG3827 110304
GTIN	4067263098416
Item class	GGN

Technical description

ISO code indexable insert	VBGT 110304
Corner radius	0.4 mm
Main application	N
Feed f	0.05 - 0.5 mm/rev.
Cutting speed v_c main application	350 - 600 mm/min
Contents	261224 HU7310
Cutting depth a_p	0.1 - 4 mm
Cutting depth $a_{p \min}$	0.25 mm
Coating	uncoated
Finishing/roughing assignment	Finishing
Tool material	Carbide
Cutting depth $a_{p \max}$	1.75 mm
Number of changes/inserts	2
Quantity	30

Tolerance	G
Type	HU7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3827 110304