

Garant**Grooving insert Full radius, CU7025, Groove width w: 4mm****Order data**

Order number	273736 4
GTIN	4045197579263
Item class	21J

Technical description

Tolerance groove width w	± 0.04 mm
Groove width w	4 mm
Feed f	0.1 - 0.22 mm/rev.
Cutting depth a_p	0.6 - 1.6 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Cermet
Coating	uncoated
Main application	P
Cutting conditions	continuous
Grade	CU7025
Number of changes/inserts	2
Indexable insert profile	neutral
Type of product	Indexable insert for grooving

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	210 m/min	P
Steel < 750 N/mm ²	suitable	170 m/min	P
Steel < 900 N/mm ²	suitable	140 m/min	P
continuous	suitable		
dry	suitable		