

Garant**VBGT indexable insert for medium machining 30 pieces, HU7310, Size: 160404****Order data**

Order number	GG3827 160404
GTIN	4067263098430
Item class	GGN

Technical description

Tool material	Carbide
Cutting speed v_c main application	350 - 600 mm/min
Contents	261232 HU7310
Coating	uncoated
Main application	N
Cutting depth $a_{p \max}$	2.5 mm
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.5 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Cutting depth a_p	0.1 - 4 mm
ISO code indexable insert	VBGT 160404
Corner radius	0.4 mm
Number of changes/inserts	2
Quantity	30

Tolerance	G
Type	HU7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3827 160404