

Garant**DCMT indexable insert for medium machining 50 pieces, HB7120-1, Size: 11T308****Order data**

Order number	GG3523 11T308
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2.75 mm
Corner radius	0.8 mm
Contents	260464 HB7120-1
Cutting depth a_p	0.5 - 2.5 mm
Quantity	50
Tolerance	M
Cutting speed v_c main application	80 - 260 mm/min
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	2
Main application	M
ISO code indexable insert	DCMT 11T308

Cutting depth $a_{p \min}$	0.55 mm
Tool material	Carbide
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3523 11T308