

Garant**KNUX indexable insert for medium machining 50 pieces, HB7130-2, Size: 160410L****Order data**

Order number	GG2937 160410L
GTIN	4067263094548
Item class	GGN

Technical description

Coating	coated
Cutting speed v_c main application	70 - 240 mm/min
Cutting depth $a_{p \min}$	0.65 mm
Cutting depth $a_{p \max}$	4 mm
Tool material	Carbide
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Corner radius	1 mm
Cutting depth a_p	0.5 - 5 mm
Quantity	50
ISO code indexable insert	KNUX 160410L
Main application	M
Number of changes/inserts	2

Contents	251038 HB7130-2
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2937 160410L