


VCGT indexable insert for finishing 30 pieces, HU7315-1, Size: 160404

Order data

Order number	GG3831 160404
GTIN	4067263092278
Item class	GGN

Technical description

ISO code indexable insert	VCGT 160404
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \max}$	2.5 mm
Coating	uncoated
Main application	N
Tool material	Carbide
Number of changes/inserts	2
Cutting speed v_c main application	50 - 600 mm/min
Cutting depth a_p	0.05 - 1.5 mm
Corner radius	0.4 mm
Cutting depth $a_{p \min}$	0.25 mm
Contents	261372 HU315-1
Feed f	0.03 - 0.25 mm/rev.
Quantity	30

Tolerance	G
Type	HU7315-1
Cutting conditions	continuous
Chip breaker	AF
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3831 160404