

**Garant****Grooving insert Full radius, HB7215, Groove width w: 2,5mm****Order data**

Order number	273737 2,5
GTIN	4045197578372
Item class	21J

**Technical description**

Groove width w	2.5 mm
Tolerance groove width w	$\pm 0.03$ mm
Feed f	0.08 - 0.16 mm/rev.
Cutting depth $a_p$	0.2 - 0.7 mm
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Main application	K
Secondary application	P
Cutting conditions	continuous
Grade	HB7215
Number of changes/inserts	2
Indexable insert profile	neutral
Type of product	Indexable insert for grooving

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 500 N/mm <sup>2</sup>	suitable	300 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	250 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	210 m/min	P
GG(G)	suitable	280 m/min	K
continuous	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		