



TCMT indexable insert for medium machining 30 pieces, HB7010-2, Size: 16T304



Order data

Order number	GG2845 16T304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting speed v_c main application	120 - 440 mm/min
Tool material	Carbide
Number of changes/inserts	3
ISO code indexable insert	TCMT 16T304
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Contents	260986 HB7010-2
Main application	P
Feed f	0.08 - 0.3 mm/rev.
Cutting depth $a_{p \max}$	4 mm
Cutting depth a_p	0.3 - 2 mm
Finishing/roughing assignment	Finishing
Quantity	30

Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2845 16T304