

Garant**SNMG indexable insert for medium machining 50 pieces, HB7130-2, Size: 120404****Order data**

Order number	GG2948 120404
GTIN	4067263094647
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4:25 mm
Coating	coated
Contents	251222 HB7130-2
ISO code indexable insert	SNMG 120404
Corner radius	0.4 mm
Quantity	50
Cutting depth a_p	0.5 - 4 mm
Cutting speed v_c main application	70 - 240 mm/min
Tool material	Carbide
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	8
Feed f	0.1 - 0.4 mm/rev.

Main application	M
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2948 120404