


SCMT indexable insert for finishing 30 pieces, HB7140-2, Size: 09T308

Order data

Order number	GG3530 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	3.25 mm
Tool material	Carbide
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	4
Main application	M
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	70 - 230 mm/min
Feed f	0.1 - 0.3 mm/rev.
ISO code indexable insert	SCMT 09T308
Contents	260744 HB7140-2
Cutting depth $a_{p \min}$	0.55 mm
Corner radius	0.8 mm
Coating	coated
Quantity	30

Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3530 09T308