



TCMT indexable insert for medium machining 50 pieces, HB7010-2, Size: 110204



Order data

Order number	GG2848 110204
GTIN	4067263092278
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Contents	260982 HB7010-2
Number of changes/inserts	3
Feed f	0.08 - 0.3 mm/rev.
Cutting depth $a_{p \min}$	0.25 mm
Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.4 mm
Cutting depth $a_{p \max}$	2.75 mm
ISO code indexable insert	TCMT 110204
Cutting speed v_c main application	120 - 440 mm/min
Quantity	50

Main application	P
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2848 110204