

Garant**SNMG indexable insert for roughing 30 pieces, HB7130-2, Size: 120408****Order data**

Order number	GG2950 120408
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.2 - 0.55 mm/rev.
Cutting depth a_p	1.5 - 7 mm
Cutting depth $a_{p \max}$	4:25 mm
Cutting speed v_c main application	60 - 220 mm/min
Tool material	Carbide
Main application	M
Cutting depth $a_{p \min}$	0.55 mm
Number of changes/inserts	8
ISO code indexable insert	SNMG 120408
Finishing/roughing assignment	Roughing
Corner radius	0.8 mm
Contents	251324 HB7130-2
Quantity	30
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2950 120408