

**Garant**
**Shrink-fit chuck, SK 40 short, Clamping range  $\varnothing$  D1: 5mm**

**Order data**

Order number	302235 5
GTIN	4045197288288
Item class	31A

**Description**
**Version:**

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID / Balluffchip bore.**

**Application:**

For clamping tools with parallel shank to h6 tolerance.  
Suitable for inductive, contact, and hot-air shrink units.

**Optional extras:**

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

**Technical description**

$\varnothing$ D <sub>2</sub>	12 mm
Overhang dimension A	80 mm
Clamping $\varnothing$ D <sub>1</sub>	5 mm
External $\varnothing$ D	17 mm
Adapter	SK 40 short
Arbor standard	ISO 7388-1

Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

## Accessories

Shrink-fit unit Type SU1	354210 SU1
Pull studForm B suitable for steep tapers 40	308640 40
Pull studsealed suitable for steep tapers 40	308635 40
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40
Pull studsealed suitable for steep tapers 40	308660 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studForm A suitable for steep tapers 40	308600 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Basic tool mountingfor SK for SK taper shank 40	354225 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 16/5 mm	302410 16/5
	308802 40

Pull stud Hurco 45° with fitsealed suitable for steep tapers 40

Pull studsealed, form B suitable for steep tapers 40

308620 40

Wrench for pull studsISO 7388 suitable for ISO taper size 40

308830 40

Pull stud 45°sealed suitable for steep tapers 40

308765 40

Shrink-fit chuck extension 4.5°without length adjustment screw  $\varnothing d / \varnothing D1$  20/5 mm

302410 20/5

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

308630 40

Cooling unit Type CU1

354215 CU1

Pull stud 45°sealed suitable for steep tapers 40

308760 40

Special pull stud with no internal threadsealed suitable for steep tapers 40

308700 40

Pull studMazak, form A suitable for steep tapers 40M

308670 40M

Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40

308801 40

Pull studMori-Seiki, sealed, form A suitable for steep tapers 40

308625 40

Pull stud Hurco 90° with fitsealed suitable for steep tapers 40

308806 40