



SCMT indexable insert for medium machining 30 pieces, HB7130-2, Size: 120408



Order data

Order number	GG3535 120408
GTIN	4067263096672
Item class	GGN

Technical description

Tool material	Carbide
Tolerance	M
ISO code indexable insert	SCMT 120408
Cutting depth $a_{p \max}$	4.25 mm
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.55 mm
Contents	260766 HB7130-2
Corner radius	0.8 mm
Cutting depth a_p	0.5 - 2.5 mm
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	70 - 240 mm/min
Quantity	30

Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3535 120408