

Garant**TNMG indexable insert for medium machining 30 pieces, HB7120-1, Size: 160404****Order data**

Order number	GG2958 160404
GTIN	4067263092278
Item class	GGN

Technical description

Tolerance	M
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	80 - 260 mm/min
Contents	251542 HB7120-1
Quantity	30
ISO code indexable insert	TNMG 160404
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	6
Main application	M
Cutting depth a_p	0.5 - 5 mm
Feed f	0.2 - 0.5 mm/rev.
Cutting depth $a_{p \max}$	4 mm
Corner radius	0.4 mm

Data sheet

Tool material	Carbide
Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2958 160404