



Shrink-fit chuck, SK 40 short, Clamping range \varnothing D1: 14mm



Order data

Order number	302251 14
GTIN	2050001689597
Item class	33W

Description

Version:

- High-temperature steel.
- Size 3 -5 for carbide, from size 6 for HSS and carbide.
- All shanks hard turned (for smooth running!).
- With RFID / Balluffchip bore.

Glass bead blasted.

Application:

For clamping tools with parallel shank to h6 tolerance.
Suitable for inductive, contact, and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Technical description

Overhang dimension A	80 mm
\varnothing D ₂	27 mm
Clamping \varnothing D ₁	14 mm
External \varnothing D	34 mm
Adapter	SK 40 short

Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 25/14 mm	302417 25/14
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/12 mm	302416 32/12
Pull studForm A suitable for steep tapers 40	308600 40
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 25/12 mm	302412 25/12
Pull studsealed, form A suitable for steep tapers 40	308610 40
Pull stud 60°sealed suitable for steep tapers 40	308785 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308630 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/12 mm	302410 25/12
Pull studMazak, form A suitable for steep tapers 40M	308670 40M
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/14 mm	302416 32/14
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Cooling unit Type CU1	354215 CU1

Pull stud 45°sealed suitable for steep tapers 40	308765 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/12 mm	302416 25/12
Shrink-fit unit Type SU1	354210 SU1
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/14 mm	302410 25/14
Pull studMori-Seiki, sealed, form A suitable for steep tapers 40	308625 40
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 40	308615 40
Pull studsealed suitable for steep tapers 40	308660 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/14 mm	302410 32/14
Pull studForm B suitable for steep tapers 40	308640 40
Shrink-fit chuck extension 4.5°without length adjustment screw, with through coolant holes Ø d / Ø D1 32/14 mm	302414 32/14
Special pull stud with no internal threadsealed suitable for steep tapers 40	308700 40
Pull studsealed, form B suitable for steep tapers 40	308650 40
Shrink fit chuck extension 3°, vibration-damped Ø d / Ø D1 20/12 mm	302415 20/12
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 32/12 mm	302410 32/12
Shrink-fit chuck extension 4.5°without length adjustment screw Ø d / Ø D1 25/14 mm	302416 25/14
Shrink-fit chuck extension 4.5°with length adjustment screw Ø d / Ø D1 25/14 mm	302412 25/14
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Screening plate for coilSU1 for clamping Ø 12-20 mm	354240 12-20
Pull stud, 18CrNiMo7Form A suitable for steep tapers 40	308605 40
Special pull stud with internal thread suitable for steep tapers 40	308740 40

Shrink-fit chuck extension 4.5° with length adjustment screw $\varnothing d / \varnothing D1$ 32/14 mm	302412 32/14
Shrink-fit chuck extension 4.5° with length adjustment screw $\varnothing d / \varnothing D1$ 32/12 mm	302412 32/12
Cooling adapter short 4.5° for clamping $\varnothing 12,1-16$ mm	354235 12,1-16
Pull stud 45° sealed suitable for steep tapers 40	308760 40
Pull stud sealed, form B suitable for steep tapers 40	308620 40
Basic tool mounting for SK for SK taper shank 40	354225 40
Cooling adapter long 4.5° for clamping $\varnothing 12,1-16$ mm	354236 12,1-16
Pull stud 90° sealed suitable for steep tapers 40	308790 40
Pull stud sealed suitable for steep tapers 40	308635 40
Wrench for pull studs ISO 7388 suitable for ISO taper size 40	308830 40