

Garant**SCMT indexable insert for medium machining 50 pieces, HB7130-2, Size: 120408****Order data**

Order number	GG3538 120408
GTIN	4067263096689
Item class	GGN

Technical description

Main application	M
Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.5 - 2.5 mm
Number of changes/inserts	4
Cutting depth $a_{p \max}$	4.25 mm
Corner radius	0.8 mm
Quantity	50
Cutting speed v_c main application	70 - 240 mm/min
ISO code indexable insert	SCMT 120408
Contents	260766 HB7130-2
Tolerance	M
Cutting depth $a_{p \min}$	0.55 mm

Data sheet

Tool material	Carbide
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3538 120408