

Garant**VNMG indexable insert for finishing 30 pieces, HB7130-2, Size: 160408****Order data**

Order number	GG2965 160408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2 mm
ISO code indexable insert	VNMG 160408
Corner radius	0.8 mm
Cutting depth $a_{p \max}$	2.5 mm
Tool material	Carbide
Feed f	0.05 - 0.4 mm/rev.
Quantity	30
Cutting depth $a_{p \min}$	0.55 mm
Cutting speed v_c main application	80 - 270 mm/min
Contents	251734 HB7130-2
Main application	M
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
Type	HB7130-2

Cutting conditions	slightly interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2965 160408