


VNMG indexable insert for finishing 30 pieces, HB7140-2, Size: 160404

Order data

Order number	GG2966 160404
GTIN	4067263092278
Item class	GGN

Technical description

Contents	251732 HB7140-2
Finishing/roughing assignment	Finishing
Feed f	0.05 - 0.4 mm/rev.
Tool material	Carbide
Quantity	30
Cutting depth a_p	0.3 - 2 mm
Cutting depth $a_{p \max}$	2.5 mm
Coating	coated
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Main application	M
Cutting speed v_c main application	70 - 230 mm/min
Number of changes/inserts	4
ISO code indexable insert	VNMG 160404

Type	HB7140-2
Cutting conditions	heavily interrupted
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2966 160404