

Garant**VCGT indexable insert for medium machining 50 pieces, HB7310, Size: 160408****Order data**

Order number	GG3838 160408
GTIN	4067263098768
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
Quantity	50
Cutting depth $a_{p \max}$	2.5 mm
Cutting speed v_c main application	350 - 600 mm/min
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	VCMT 160404
Feed f	0.05 - 0.5 mm/rev.
Contents	261459 HB7310
Tool material	Carbide
Cutting depth a_p	0.1 - 4 mm
Number of changes/inserts	2
Main application	N

Tolerance	M
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3838 160408