

**Value pack CNMG indexable insert medium machining 30 pieces HBT020****Order data**

Order number	GG3902 160608
GTIN	4067263092551
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	5.5 mm
ISO code indexable insert	CNMG 160608
Coating	TiCN
Finishing/roughing assignment	Finishing
Tool material	Carbide
Main application	P
Cutting depth a_p	0.8 - 5 mm
Corner radius	0.8 mm
Number of changes/inserts	4
Contents	250204 HBT020
Cutting speed v_c main application	100 - 280 mm/min
Cutting depth $a_{p \min}$	0.55 mm
Feed f	0.1 - 0.45 mm/rev.
Quantity	30

Type	HBT020
Cutting conditions	slightly interrupted
Chip breaker	PM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3902 160608