

Garant**VBMT indexable insert for finishing 30 pieces, HB7035-2, Size: 160402****Order data**

Order number	GG2854 160402
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	2
Cutting depth a_p	0.2 - 1.5 mm
Contents	261150 HB7035-2
Main application	P
Feed f	0.07 - 0.25 mm/rev.
Cutting depth $a_{p \max}$	2.5 mm
Tool material	Carbide
Cutting speed v_c main application	120 - 350 mm/min
Cutting depth $a_{p \min}$	0.15 mm
Corner radius	0.2 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	VBMT 160402
Quantity	30
Type	HB7035-2

Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2854 160402