

**VBMT indexable insert for finishing 50 pieces, HB7020-2, Size: 110304****Order data**

Order number	GG2856 110304
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	VBMT 110304
Quantity	50
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	140 - 400 mm/min
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Contents	261144 HB7020-2
Cutting depth $a_{p \max}$	1.75 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Tool material	Carbide

Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2856 110304