

Garant**VBMT indexable insert for medium machining 50 pieces, HB7010-2, Size: 110304****Order data**

Order number	GG2861 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Cutting speed v_c main application	120 - 440 mm/min
Contents	261224 HB7010-2
Corner radius	0.4 mm
Tool material	Carbide
Cutting depth a_p	0.3 - 2 mm
ISO code indexable insert	VBMT 110304
Cutting depth $a_{p \max}$	1.75 mm
Main application	P
Feed f	0.08 - 0.3 mm/rev.

Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2861 110304