

Garant**TCMT indexable insert for finishing 50 pieces, HB7120-1, Size: 16T308****Order data**

Order number	GG3543 16T308
GTIN	4067263092278
Item class	GGN

Technical description

Quantity	50
ISO code indexable insert	TCMT 16T308
Cutting depth $a_{p \min}$	0.5 mm
Main application	M
Corner radius	0.8 mm
Contents	260958 HB7120-1
Cutting depth $a_{p \max}$	4 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	90 - 290 mm/min
Number of changes/inserts	3
Feed f	0.1 - 0.3 mm/rev.
Tool material	Carbide

Type	HB7120-1
Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3543 16T308