

Garant**VBMT indexable insert for medium machining 50 pieces, HB7020-2, Size: 160408****Order data**

Order number	GG2862 160408
GTIN	4067263095903
Item class	GGN

Technical description

Contents	261234 HB7020-2
Number of changes/inserts	2
Corner radius	0.8 mm
Feed f	0.08 - 0.3 mm/rev.
Main application	P
ISO code indexable insert	VBMT 160408
Cutting depth $a_{p \max}$	2.5 mm
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
Cutting speed v_c main application	110 - 350 mm/min
Tool material	Carbide
Cutting depth $a_{p \min}$	0.55 mm

Data sheet

Quantity	50
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2862 160408