

Garant**VCMT indexable insert for finishing 30 pieces, HB7010-2, Size: 110302****Order data**

Order number	GG2864 110302
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 1.5 mm
ISO code indexable insert	VCMT 110302
Cutting depth $a_{p \max}$	1.75 mm
Number of changes/inserts	2
Tolerance	M
Main application	P
Cutting speed v_c main application	150 - 500 mm/min
Tool material	Carbide
Cutting depth $a_{p \min}$	0.15 mm
Contents	261364 HB7010-2
Feed f	0.07 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Corner radius	0.2 mm
Quantity	30

Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2864 110302