

Garant**VCMT indexable insert for finishing 30 pieces, HB7020-2, Size: 110304****Order data**

Order number	GG2865 110304
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.25 mm
Main application	P
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	140 - 400 mm/min
Cutting depth $a_{p \max}$	1.75 mm
Tool material	Carbide
Corner radius	0.4 mm
ISO code indexable insert	VCMT 110304
Tolerance	M
Contents	261366 HB7020-2
Number of changes/inserts	2
Feed f	0.07 - 0.25 mm/rev.
Finishing/roughing assignment	Finishing
Quantity	30

Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2865 110304