

**Garant**
**TC.T 110202, Grade: HB7120-1**


### Order data

Order number	260980 HB7120-1
GTIN	4045197818744
Item class	21G

### Description

TC.T 110202 HB7120-1 Grade: HB7120-1  
 Chip breaker: VM  
 Tolerance: M  
 Cutting depth  $a_p$ : 0.5 - 2.5 mm  
 Feed  $f$ : 0.1 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 80 - 260 m/min

### Technical description

Feed $f$	0.1 - 0.4 mm/rev.
Chip breaker	VM
Grade	HB7120-1
Cutting speed $v_c$ main application	80 - 260 m/min
Corner radius	0.2 mm
Cutting conditions	continuous
Cutting depth $a_p$	0.5 - 2.5 mm
Main application	M

Finishing/roughing assignment	Semi-roughing
Tool material	Carbide
ISO code indexable insert	TCMT 110202
Number of changes/inserts	3
Tolerance	M
Type of product	Indexable insert for turning