

Garant
VBMT 160404, Grade: HB7120-1


Order data

Order number	261152 HB7120-1
GTIN	4045197818812
Item class	21G

Description

VBMT 160404 HB7120-1 Grade: HB7120-1
 Chip breaker: VS
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.1 - 0.3 mm/rev.
 Cutting speed v_c main application: 90 - 290 m/min

Technical description

Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	90 - 290 m/min
Chip breaker	VS
Main application	M
Grade	HB7120-1
Cutting depth a_p	0.2 - 1.5 mm
Cutting conditions	continuous

Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	VBMT 160404
Number of changes/inserts	2
Type of product	Indexable insert for turning