

Garant**WNMG indexable insert for finishing 30 pieces, HB7120-1, Size: 080404****Order data**

Order number	GG2976 080404
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Contents	251962 HB7120-1
Corner radius	0.4 mm
Main application	M
Feed f	0.1 - 0.4 mm/rev.
Cutting depth $a_{p \max}$	2.75 mm
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.25 mm
Number of changes/inserts	6
Cutting speed v_c main application	90 - 290 mm/min
ISO code indexable insert	WNMG 080404
Quantity	30
Type	HB7120-1

Cutting conditions	continuous
Chip breaker	VS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2976 080404